

# FL216B

**Polyester enclosure, Orion.Plus, plain door 650x400x200 mm**

## Architecture

Fixing mode	Wall mounting
-------------	---------------

## Main electrical features

Rated current	630 A
---------------	-------

## Dimensions

Depth of installed product	200 mm
----------------------------	--------

Height of installed product	650 mm
-----------------------------	--------

Width of installed product	400 mm
----------------------------	--------

## Capacity

Number of modules	72
-------------------	----

## Cover, door

Type of door closing	lock with male triangular wrench
----------------------	----------------------------------

Number of keylock of the door	2
-------------------------------	---

Interlockable	Yes
---------------	-----

---

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
RAL colour number	7035
Material	glas reeinforced polyester
Type of surface treatment	untreated

Equipment

Number of rows	4
Can be accessorized	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP66
Protection class	isol.class II