



### Steel enclosure, Orion.Plus, glazed door 950x800x300 mm

#### Technical Characteristics

Fixing mode	Wall mounting
Rated current	630 A
Depth of installed product	300 mm
Height of installed product	950 mm
Width of installed product	800 mm
Number of modules	222
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
RAL colour number	7035
Material	Steel
Type of surface treatment	powder-coated
Number of rows	6
Can be accessorized	No
European directive WEEE	not concerned
Protection index IP	IP65
Protection class	isol.class I