

SM100

Analogue ammeter 0-100A indirect reading



- Architecture
 - Fixing mode
Din-Rail
- Main electrical features
 - Frequency
45;65 Hz
- Voltage
 - Rated insulation voltage
2000 V
- Dimensions
 - Depth of installed product
54 mm
 - Height of installed product
85 mm
 - Width of installed product
70 mm
- Power
 - Power consumed
1.1 VA
 - Total power loss under IN
1.1 W
- Measurement
 - Type of measuring instrument
ammeter
- Capacity
 - Number of modules
4

- Connection
 - Connection cross-sect. flexible conductor
1 ; 6mm²
 - Connection cross-sect. rigid cable
1,5 ; 10mm²
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-40/80 °C
- Temperature
 - Operating temperature
-25/50 °C