

# WFPS22BSB

**10AX 2 Gang 2 Way Wall Switch Brushed Steel Black Insert**

## Configuration

Switch mode 2 way

---

## Main electrical features

Rated current 10 AX

---

## Dimensions

Depth 24 mm

---

Height 86 mm

---

Width 86 mm

---

## Frequency

Frequency 50;60 Hz

---

## Materials

Colour stainless steel optics

---

Material stainless steel

---

## Installation, mounting

**Imprint** with clear terminal markings

---

Connection

**Terminal** unique patented loop terminal allows neutral looping at the switch

---

Scope of delivery

**Component** with 2 fixing screws M3.5 x 20 mm

---

Equipment

**Lighting** without lighting (cannot be illuminated)

---

Standards

**Standard** BS EN 60669-1

---

Use conditions

**Insert** insert, black

---