

WFPS32BSW

10AX 3 Gang 2 Way Wall Switch Brushed Steel White Insert

Configuration

Switch mode 2 way

Main electrical features

Rated current 10 AX

Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

Frequency

Frequency 50;60 Hz

Materials

Colour stainless steel optics

Material stainless steel

Installation, mounting

Imprint	with clear terminal markings
Connection	
Terminal	unique patented loop terminal allows neutral looping at the switch
Scope of delivery	
Component	with 2 fixing screws M3.5 x 20 mm
Equipment	
Lighting	without lighting (cannot be illuminated)
Standards	
Standard	BS EN 60669-1
Use conditions	
Insert	insert white