



Weekly digital time switch 2 channels, digital, 2 modules

Technical Characteristics

Bus system	
Fixing mode	Din-Rail
Function	Keylock by means of blocking key
Bus system radio frequent	No
Frequency	50 Hz
Type of supply voltage	
Supply voltage	230V AC
Breaking capacity	16A 250V AC1
Colour	
RAL colour number	
Max. power fluo. duo lamp comp. series	
Tightening torque	
Mounting type	
Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of load	
Type of connection	with screw
Type of contacts	2 changeovers
Type of connection	with screw terminals
Summer / Winter time change	automatic
Shortest switching time	1 mn
Astronomic program	
Type of programming	digital
Programming cycle	2X7D.
Type of display	
Type of programmable thermostat	
Supply failure reserve	5 years
Quick connect	
With holidays program	No

DCF	No
Cycle	weekly
Protection index IP	IP20
Working accuracy	1,5