



1 channel weekly programmer

Technical Characteristics

Fixing mode	Din-Rail
Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Supply voltage	230V AC
Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm
Power consumed	4 VA
Total power loss under IN	4 W
Breaking capacity	16A 250V AC1
Number of modules	2
Power reserve [years]	≈ 99 a
Max. power with incandescent lamps	1000 W
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Summer / Winter time change	manual
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.
Number of channels	1
Supply failure reserve	programming unlimited
With holidays program	No
DCF	No
Cycle	weekly
Protection index IP	IP20
Operating temperature	45 °C -5 °C
Working accuracy	5