

WRPS22PSB

10AX 2 Gang 2 Way Wall Switch Polished Steel Black Insert

Configuration

Switch mode 2 way

Main electrical features

Rated current 10 AX

Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

Frequency

Frequency 50;60 Hz

Materials

Colour silver optics

Material stainless steel

Installation, mounting

Imprint with clear terminal markings

Connection

Terminal unique patented loop terminal allows neutral looping at the switch

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Equipment

Lighting without lighting (cannot be illuminated)

Standards

Standard BS EN 60669-1

Use conditions

Insert insert, black
