



### Under voltage release for motor starter 230V AC

#### Technical Characteristics

Rated operational voltage U <sub>e</sub>	230 V
Frequency	50 Hz
Type of supply voltage	AC
Rated insulation voltage	6000 V
Depth of installed product	68 mm
Width of installed product	17.5 mm
Total power loss under I <sub>N</sub>	0.5 W
Number of modules	1
Connection cross-sect. flexible conductor	2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	2,5mm <sup>2</sup>
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-25 °C 55 °C