



### Under voltage release 230V AC

#### Technical Characteristics

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Type of supply voltage	AC
Rated insulation voltage	4000 V
Acceptable current rating with AC1	15 mA
Depth of installed product	68 mm
Width of installed product	17.5 mm
Total power loss under IN	2 W
Number of modules	1
Tightening torque	1,2Nm
Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>
Can be accessorized	No
European directive WEEE	concerned
Operating temperature	60 °C -25 °C