

75642134

KNX glass sensor 2g thermostat, display, intg bus coupl , KNX-TS sensor, al.

Architecture

Fixing mode flush-mounting

Functions

Function with valve protection function ; for switch, push-button, dimmer, blind and thermostat functions

Voltage

Operating voltage 21 ... 32 V DC

Dimensions

Depth 37.7 mm

Height 160 mm

Width 86 mm

Power

Current consumption 23 mA

Materials

Colour aluminium

RAL colour	RAL 9006 - White aluminium
Material	glass
Surface appearance	glossy
Type of surface treatment	Tampography
Accessories included	
Inscribable, with labelling field	No
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-5/45 °C
Identification	
Designation syntax: Core designation/function	Glass sensor
Application, usage	KNX - operating systems