



### Architrave Socket c/w Trunking Clamp

#### Technical Characteristics

	253 V
	207 V
Rated operational voltage Ue	230 V
Rated current	6 A
Colour	pure white
Number of terminations -sockets	4
Contact Material	Phosphor Bronze
Inflammability	UL 94 V0
Application, usage	Light control