

FL168A

Steel enclosure, Orion.Plus, glazed door 650x400x250 mm



Architecture

Fixing mode Wall mounting

Dimensions

Depth of installed product 250 mm

Height of installed product 650 mm

Width of installed product 400 mm

Capacity

Number of modules 72

Cover, door

Type of door closing lock with male triangular wrench

Interlockable Yes

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Technical characteristics FL168A

RAL colour number	7035
Material	Steel
Type of surface treatment	powder-coated
Equipment	
Number of rows	4
Safety	
Protection index IP	IP65
Protection class	isol.class I