

FL259B

Polyester enclosure, Orion.Plus, glazed door 500x300x200 mm

Architecture

Fixing mode	Wall mounting
-------------	---------------

Main electrical features

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	200 mm
----------------------------	--------

Height of installed product	500 mm
-----------------------------	--------

Width of installed product	300 mm
----------------------------	--------

Capacity

Number of modules	36
-------------------	----

Cover, door

Type of door closing	lock with male triangular wrench
----------------------	----------------------------------

Number of keylock of the door	2
-------------------------------	---

Interlockable	Yes
---------------	-----

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
RAL colour number	7035
Material	glas reeinforced polyester
Type of surface treatment	untreated

Equipment

Number of rows	3
Can be accessorized	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP66
Protection class	isol.class II