

FL279B

Polyester enclosure, Orion.Plus, glazed door 800x600x300 mm



- Architecture
 - Fixing mode
Wall mounting
- Main electrical features
 - Rated current
630 A
- Dimensions
 - Depth of installed product
300 mm
 - Height of installed product
800 mm
 - Width of installed product
600 mm
- Capacity
 - Number of modules
140
- Cover, door
 - Type of door closing
lock with male triangular wrench
 - Number of keylock of the door
2
 - Interlockable
Yes
- Materials
 - Colour
RAL 7035
 - Colour

- light grey
- RAL colour
RAL 7035 - Light grey
- RAL colour number
7035
- Material
glas reeinforced polyester
- Type of surface treatment
untreated
- Equipment
 - Number of rows
5
 - Can be accessorized
No
- Standards
 - European directive WEEE
not concerned
- Safety
 - Protection index IP
IP66
 - Protection class
isol.class II