



Fuse carrier 1P 32A 415V BS88 1M

Technical Characteristics

Type of pole	1 P
Indicator lamp	no
Rated operational voltage Ue	415 V
Frequency	50/60 Hz
Rated current	32 A
Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	18 mm
Total power loss under IN	3.63 W
Electric endurance in number of cycles	2000
Number of mechanical operations	4000
Number of modules	1
Interlockable	No
Tightening torque	2,2Nm
Connection cross-sect. flexible conductor	0,75 / 16mm ²
Connection cross-sect. rigid cable	1 / 25mm ²
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20