



### Fuse carrier 1P+N 32A 400V 1M

#### Technical Characteristics

Number of poles	2 P
Type of pole	1P+N
Indicator lamp	no
Rated operational voltage Ue	400 V
Frequency	50 Hz
Rated current	32 A
Depth of installed product	75 mm
Height of installed product	77 mm
Width of installed product	17.5 mm
Total power loss under IN	1.5 W
Electric endurance in number of cycles	2000
Number of mechanical operations	5000
Number of modules	1
Interlockable	No
Tightening torque	1,8Nm
Connection cross-sect. flexible conductor	10mm <sup>2</sup>
Connection cross-sect. rigid cable	16mm <sup>2</sup>
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-5 °C 40 °C