



4-pole, 125A Modular Switch

Technical Characteristics

Neutral position	without neutral
Type of pole	4 P
Frequency	50/60 Hz
Type of supply voltage	
Colour	
Type of lamp	
Tightening torque	3,6Nm
Connection cross-sect. flexible conductor	6 / 35mm ²
Connection cross-sect. rigid cable	6 / 50mm ²
Type of connection	with screw
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20