



1-pole, 25A Modular Switch with Indicator Light

Technical Characteristics

Neutral position	without neutral
Number of poles	1 P
Type of pole	1 P
Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Rated current	25 A
Rated insulation voltage	440 V
Rated impulse withstand voltage	4000 V
Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	17.5 mm
Total power loss under IN	1 W
Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000
Number of modules	1
Type of lamp	LED
Tightening torque	1,8Nm
Connection cross-sect. flexible conductor	1,5 / 10mm ²
Connection cross-sect. rigid cable	1,5 / 16mm ²
Type of connection	with screw
Can be accessorized	No
Standard text	IEC 60947-3 IEC/EN 60669-1
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-20 °C 50 °C