

WMPS32

10AX 3 Gang 2 Way Wall Switch



More Information

Symbols for applications	LOOP-TERMINAL_APP-SYMBOL.EPS
Color_Label	white
Colour of design line	white
Colour independent of design lines	white
Design lines special colours	white
Conductor cross-section	2 x 4 mm ²
Depth	24 mm
Height	86 mm
Insertion depth	12 mm
Colour	white
Material	Urea-formaldehyde
Standard	BS EN 60669-1
Rated current	10 AX
Appliance switch type	No
Component	with 2 fixing screws M3.5 x 30 mm
Imprint	with clear terminal markings

Installation mode	for flush-mounted and hollow-wall mounting
Labelling	without labelling
Lighting	without lighting (cannot be illuminated)
Push-buttons	No
Switch mode	2 way
Terminal	unique patented loop terminal allows neutral looping at the switch
Width	86 mm
Unit	PCE
EAN	5015652260851
Sales status	3C