

WMPS62

10AX 6 Gang 2 Way Wall Switch

Configuration

Switch mode 2 way

Main electrical features

Rated current 10 AX

Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

Frequency

Frequency 50;60 Hz

Materials

Colour white

Material Urea-formaldehyde

Installation, mounting

Imprint	with clear terminal markings
<hr/>	
Connection	
Terminal	unique patented loop terminal allows neutral looping at the switch
<hr/>	
Scope of delivery	
Component	with 2 fixing screws M3.5 x 30 mm
<hr/>	
Equipment	
Lighting	without lighting (cannot be illuminated)
<hr/>	
Standards	
Standard	BS EN 60669-1
<hr/>	