

WPPS22B

10AX 2 Gang 2 Way Wall Switch & Back Box without Knockouts

Configuration

Switch mode 2 way

Main electrical features

Rated current 10 AX

Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

Frequency

Frequency 50;60 Hz

Materials

Colour grey

Material Steel

Installation, mounting

Imprint with clear terminal markings

Connection

Terminal unique patented loop terminal allows neutral looping at the switch

Scope of delivery

Component with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each

Equipment

Lighting with control LED for ON

Standards

Standard BS EN 60669-1
