

TXA111

Power supply 30V DC 320 mA

Architecture

Bus system	EIB
Fixing mode	Din-Rail

Main electrical features

Frequency	50;60 Hz
-----------	----------

Voltage

Supply voltage	230V AC
----------------	---------

Fuse

Fuse	with electronic short-circuit and overload protection
------	---

Dimensions

Depth of installed product	64 mm
Height of installed product	90 mm
Length	64 mm
Width of installed product	72 mm

Frequency

Frequency 50;60 Hz

Power

Total power loss under IN 15 W

Capacity

Number of modules 4

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Connection

Connection cross-sect. flexible conductor 0,75 ; 2,5mm²

Connection cross-sect. rigid cable 0,75 ; 2.5mm²

Type of connection quick connect

Type of connection with QuickConnect plug-in terminals

Safety

Protection index IP IP20

Use conditions

Operating temperature -5/45 °C

Storage temperature -20/70 °C

Temperature

Operating temperature -5/45 °C
