

TXA114

Power supply 1x 30V DC + 1x 24V DC

Architecture

| | |
|-------------|----------|
| Bus system | EIB |
| Fixing mode | Din-Rail |

Main electrical features

| | |
|-----------|----------|
| Frequency | 50;60 Hz |
|-----------|----------|

Fuse

| | |
|------|---|
| Fuse | with electronic short-circuit and overload protection |
|------|---|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 64 mm |
| Height of installed product | 90 mm |
| Length | 64 mm |
| Width of installed product | 72 mm |

Frequency

| | |
|-----------|----------|
| Frequency | 50;60 Hz |
|-----------|----------|

Power

Total power loss under IN 4.4 W

Capacity

Number of modules 4

Materials

RAL colour RAL 7035 - Light grey

Connection

Connection cross-sect. flexible conductor 0,75 ; 2,5mm²

Connection cross-sect. rigid cable 0,75 ; 2.5mm²

Type of connection with QuickConnect plug-in terminals

Safety

Protection index IP IP20

Use conditions

Operating temperature -5/45 °C

Storage temperature -20/70 °C

Temperature

Operating temperature -5/45 °C
