

# WFSSU83FOPSW

13A FCU Switched with Flex Outlet Polished Steel White Insert

## Configuration

Switch mode 2pole

---

## Main electrical features

Rated current 13 A

---

## Fuse

Fuse with ceramic fine fuse F 13A

---

## Dimensions

Depth 30.3 mm

---

Height 86 mm

---

Width 86 mm

---

## Frequency

Frequency 50;60 Hz

---

## Materials

Colour silver optics

---

---

<b>Material</b>	stainless steel
-----------------	-----------------

---

Installation, mounting

<b>Imprint</b>	with clear terminal markings
----------------	------------------------------

---

Cable

<b>Wiring</b>	with double earth connection
---------------	------------------------------

---

Scope of delivery

<b>Component</b>	with 2 fixing screws M3.5 x 20 mm
------------------	-----------------------------------

---

Equipment

<b>Lighting</b>	without lighting (cannot be illuminated)
-----------------	--

---

Standards

<b>Standard</b>	BS 1363-4
-----------------	-----------

---

Safety

<b>Protection</b>	to protect downstream loads
-------------------	-----------------------------

---

Use conditions

<b>Insert</b>	insert white
---------------	--------------

---