

# SFT225

## 2-pole, 25A Centre Off Modular Changeover Switch with Top Common Point



- Architecture
  - Number of poles  
2 P
  - Type of pole  
2 P
- Main electrical features
  - Frequency  
50/60 Hz
  - Rated current  
25 A
- Voltage
  - Rated insulation voltage  
440 V
  - Rated impulse withstand voltage  
4000 V
- Dimensions
  - Depth of installed product  
70 mm
  - Height of installed product  
83 mm
  - Width of installed product  
35 mm
- Power
  - Total power loss under IN  
1.8 W
- Endurance
  - Electrical durability at nominal load in AC22 in operating cycles

- 25000
- Number of mechanical operations  
200000
- Capacity
  - Number of modules  
2
- Installation, mounting
  - Tightening torque  
1,8Nm
- Connection
  - Connection cross-sect. flexible conductor  
1,5 / 10mm<sup>2</sup>
  - Connection cross-sect. rigid cable  
1,5 / 16mm<sup>2</sup>
  - Type of connection  
with screw
- Equipment
  - Can be accessorized  
No
- Standards
  - Standard text  
IEC/EN 60669-1  
IEC 60947-3
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP20
- Use conditions
  - Storage temperature  
-40/80 °C
- Temperature
  - Operating temperature  
-20/50 °C