

WK060

Rotary dimmer for eco lamps, kallysta



- Architecture
 - Fixing mode
flush-mounting
- Main electrical features
 - Frequency
50/60 Hz
 - Rated current
1.5 A
- Voltage
 - Supply voltage
230V AC
- Dimensions
 - Height of installed product
70 mm
 - Dimensions (LLxwwxhh)
71x71x35
 - Width of installed product
70 mm
- Power
 - Max. power with electronic transfo.
250 VA
- Materials
 - RAL colour
RAL 7047 - Telegrey 4
 - Material
polycarbonate
 - Material

- Polycarbonate (PC)
- Surface appearance
other
- Type of surface treatment
untreated
- Installation, mounting
 - Mounting type
flush-mounted
- Connection
 - Type of load
universal
 - Type of connection
with screw
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-10/50 °C
- Temperature
 - Operating temperature
-10/35 °C