

WE064

Essensya Rotative dimmer 320VA electro transformer

:hager

- Architecture
 - Fixing mode
flush-mounting
- Main electrical features
 - Frequency
50/60 Hz
- Voltage
 - Supply voltage
230V AC
- Dimensions
 - Depth of installed product
48 mm
 - Height of installed product
70 mm
 - Width of installed product
70 mm
- Materials
 - Colour
white
 - RAL colour
RAL 9010 - Pure white
 - RAL colour number
9010
 - Material
polycarbonate
 - Material
Polycarbonate (PC)

- Surface appearance
glossy
- Type of surface treatment
Painted
- Installation, mounting
 - Mounting type
flush-mounted
- Connection
 - Connection cross-sect. flexible conductor
1,5 / 2,5mm²
 - Connection cross-sect. rigid cable
mini 2x1 mm² - maxi 2x2,5 mm²
 - Type of connection
with screw
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-10/50 °C
- Temperature
 - Operating temperature
-10/35 °C