

EN145

Interface relay VLV/ LV

Main electrical features

Rated operational voltage Ue	250 V
Frequency	50;60 Hz
Rated current	5 A

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Electric current

Acceptable current rating with AC1	5 A
------------------------------------	-----

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	2 W
---------------------------	-----

Capacity

Number of modules	1
-------------------	---

Connection

Connection cross-sect. flexible conductor 0,5 ; 4mm²

Connection cross-sect. rigid cable	1 ; 6mm ²
------------------------------------	----------------------

Type of connection	with screw
--------------------	------------

Number of contacts	1
--------------------	---

Type of contacts	1 changeover
------------------	--------------

Equipment

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Storage temperature	-40/80 °C
---------------------	-----------

Temperature

Operating temperature	-10/50 °C
-----------------------	-----------
