

EN146

Interface relay LV / VLV



Main electrical features

Rated operational voltage U_e	250 V
Frequency	50;60 Hz
Rated current	5 A

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	2 W
---------------------------	-----

Capacity

Number of modules	1
-------------------	---

Connection

Connection cross-sect. flexible conductor 0,5 ; 4mm²

Connection cross-sect. rigid cable 1 ; 6mm²

Type of connection with screw

Number of contacts 1

Type of contacts 1 changeover

Standards

European directive WEEE concerned

Use conditions

Storage temperature -40/80 °C

Temperature

Operating temperature -10/50 °C
