

WMGS16BSW

20A Intermediate Switch Brushed Steel White Insert

Configuration

Switch mode	intermediate
-------------	--------------

Main electrical features

Rated current	20 A
---------------	------

Dimensions

Depth	24 mm
-------	-------

Height	60 mm
--------	-------

Width	25 mm
-------	-------

Frequency

Frequency	50;60 Hz
-----------	----------

Materials

Colour	stainless steel optics
--------	------------------------

Material	duroplastic
----------	-------------

Installation, mounting

Imprint with clear terminal markings

Equipment

Lighting without lighting (cannot be illuminated)

Use conditions

Insert insert white

Identification

Designation syntax: Core designation/function Intermediate switch
