

# WMGS16PSB

## 20A Intermediate Switch Polished Steel Black Insert

### Configuration

Switch mode	intermediate
-------------	--------------

### Main electrical features

Rated current	20 A
---------------	------

### Dimensions

Depth	24 mm
-------	-------

Height	59 mm
--------	-------

Width	25 mm
-------	-------

### Frequency

Frequency	50;60 Hz
-----------	----------

### Materials

Colour	silver optics
--------	---------------

Material	duroplastic
----------	-------------

### Installation, mounting

Imprint	with clear terminal markings
Equipment	
Lighting	without lighting (cannot be illuminated)
Use conditions	
Insert	insert, black
Identification	
Designation syntax: Core designation/function Intermediate switch	