



SPD pluggable photovoltaic 25kA class 2

Technical Characteristics

| | |
|--|-------------------------|
| Type of pole | 2 P |
| Indicator lamp | reserve |
| With remote signalling contact | No |
| Frequency | 50/60 Hz |
| Max discharge (I _{max}) or impulse (I _{imp}) | 25 kA |
| Width of installed product | 54 mm |
| Number of modules | 3 |
| Connection cross-sect. flexible conductor | 1,5 / 25mm ² |
| Connection cross-sect. rigid cable | 1,5 / 35mm ² |
| European directive WEEE | concerned |
| Operating temperature | 40 °C 80 °C |