



SPD 2P pluggable 8kA class 2 with indicator

Technical Characteristics

Type of pole	1P+N
Indicator lamp	reserve
With remote signalling contact	No
Rated operational voltage Ue	230 V
Max discharge (Imax) or impulse (Iimp)	8 kA
Width of installed product	35 mm
Total power loss under IN	0.1 W
Number of modules	2
Connection cross-sect. flexible conductor	25mm ²
Connection cross-sect. rigid cable	35mm ²
European directive WEEE	concerned
Operating temperature	80 °C
	40 °C