

# Product data sheet

KDN263B

**:hager**



## Insulated busbar 2P 63A fork 10mm<sup>2</sup> 57M

### Technical Characteristics

Number of poles	2 P
Rated current	63 A
Max operating voltage	400 V
Length	1000 mm
Colour	stone grey
Connection cross-sect. rigid cable	10mm <sup>2</sup>
Type of connection	with screw / quick connect
European directive WEEE	concerned