



### EARTH LEAKAGE RELAY 0.03A INSTANT TRIP

#### Technical Characteristics

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Max operating voltage	276 V
Acceptable current rating with AC1	8 A
Rated residual operating current	30 mA
Maximum connection distance between receiver and transmitter	25m and 50m twisted pair
Power consumed	3 VA
Total power loss under IN	4.2 W
Number of modules	1
Tightening torque	1,7Nm
Connection cross-sect. flexible conductor	1 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 4mm <sup>2</sup>
Type of contacts	Stand 1 OF
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP30
Residual current type	A
Operating temperature	-10 °C 55 °C