



### 2 flush mounted battery inputs

#### Technical Characteristics

Fixing mode	flush-mounting
Indicator lamp	lighting indicator
Supply voltage	1 lithium battery 3V CR 1/2 AA
Dimensions (LLxwwxhh)	48 x 53 x 30 mm
Total power loss under IN	0.4 W
Max. transmission range	30m in house / 100m free field
Colour	stone grey
Connection cross-sect. flexible conductor	0,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,5 / 2,5mm <sup>2</sup>
Protection index IP	IP30
Operating temperature	45 °C 0 °C