

# TU406

## 6-channel remote control



- Architecture
  - Number of keys  
6
  - Fixing mode  
other
- Functions
  - Function  
easy additional functions: +6 scenes, on ; off operating mode, 1 up ; down button control ; reset function (to factory setting)
- Voltage
  - Supply voltage  
2 lithium batteries 3V CR2430
- Dimensions
  - Depth of installed product  
16 mm
  - Height of installed product  
133.6 mm
  - Dimensions (LLxwwxhh)  
133,6 x 50,2 x 16 mm
  - Width of installed product  
50.2 mm
- Reach distance
  - Max. transmission range  
30m in house ; 100m free field
- Safety
  - Protection index IP  
IP30

- Use conditions
  - Operating temperature  
0/45 °C
- Temperature
  - Operating temperature  
0/45 °C