



JK216 96 Module Side DIN Box Glazed

Technical Characteristics

Fixing mode	surface-mounting
Rated current	250 A
Depth of installed product	165.5 mm
Height of installed product	1250 mm
Width of installed product	465 mm
Number of modules	96
Type of door closing	Quarter turn lock
Door locking	with key
Interlockable	No
Colour	beige
RAL colour	RAL 1001 - Beige
RAL colour number	7035
Material	Steel
Number of rows	6
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP3X
Protection class	Protection class III