



20A Double Pole Switch with LED Indicator and Flex Outlet & Back Box without Kno

Technical Characteristics

Switch mode	2pole
Frequency	50/60 Hz
Depth	53.2 mm
Height	86 mm
Width	86 mm
Colour	grey
Material	Steel
Imprint	with clear terminal markings
Component	with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
Lighting	with control LED for ON
Designation syntax: Core designation/function	Switch