



20A Double Pole Switch with LED Indicator Marked TUMBLEDRYER

Technical Characteristics

| | |
|---|--------------------------------------|
| Switch mode | 2pole |
| Frequency | 50/60 Hz |
| Depth | 32.8 mm |
| Height | 86 mm |
| Width | 86 mm |
| Colour | white |
| Material | Urea-formaldehyde |
| Imprint | with clear terminal markings |
| Component | with 2 fixing screws M3.5 x 30 mm |
| Lighting | with control LED for ON |
| Designation syntax: Core designation/function | Switch |