



### Twilight switch 1 channel, 1M, wall mounted cell

#### Technical Characteristics

Bus system	
Fixing mode	Din-Rail
Frequency	50/60 Hz
Supply voltage	
Maximum connection distance between receiver and transmitter	100m
Breaking capacity	10A 250V AC1
Supply voltage	230 V
Colour	
Max. power fluo. duo lamp comp. series	1000 W
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1,5 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 6mm <sup>2</sup>
Type of connection	
Type of contacts	contact floating
Type of connection	with screw terminals
Summer / Winter time change	
Shortest switching time	
Astronomic program	
Programming cycle	
Type of display	
Supply failure reserve	
With holidays program	No
Cycle	
Protection index IP	IP20
Working accuracy	