

Product data sheet

TYF120

:hager



Interface KNX/IP, 2 modules, IP20

Technical Characteristics

Bus system	KNX
Fixing mode	Din-Rail
Bus system radio frequent	No
Supply voltage	30V DC via Bus
Bus consumption	10 mA
Dimensions (W x H x D)	36 mm 58 mm 90 mm
Number of modules	2
RAL colour	RAL 7035 - Light grey
Type of connection	Bus KNX/EIB + Ethernet (10 Mbit/s)
Connection type	TG008 (bus and supply voltage) / RJ45 (Ethernet)
Type of connection	operating voltage connection via connecting terminal with RJ45 connection for Ethernet;IP networks
Protection index IP	IP20
Operating temperature	45 °C -5 °C
Designation syntax: Core designation/function	Gateway