



Analogue ammeter 0-400A indirect reading

Technical Characteristics

Fixing mode	Din-Rail
Frequency	45/65 Hz
Type of measuring instrument	ammeter
Mounting type	
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of display	
Protection index IP	IP20