



Analogue ammeter 0-100A indirect reading

Technical Characteristics

Fixing mode	Din-Rail
Frequency	45/65 Hz
Rated insulation voltage	2000 V
Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm
Power consumed	1.1 VA
Total power loss under IN	1.1 W
Type of measuring instrument	ammeter
Number of modules	4
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Protection index IP	IP20
Operating temperature	-25 °C 50 °C