

ST305

Bell transformer 16VA 230V 8-12V



- Architecture
 - Fixing mode
DIN rail type O (symmetrical)
- Main electrical features
 - Frequency
50 Hz
- Voltage
 - Rated insulation voltage
4000 V
- Dimensions
 - Depth of installed product
65 mm
 - Height of installed product
111 mm
 - Width of installed product
54 mm
- Power
 - Power consumed
16 VA
 - Total power loss under IN
1.8 W
- Capacity
 - Number of modules
3
- Installation, mounting
 - Tightening torque
1,2Nm

- Connection
 - Connection cross-sect. flexible conductor
4mm²
 - Connection cross-sect. rigid cable
6mm²
- Standards
 - Standard text
EN 61558-2-6
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Temperature
 - Operating temperature
-20/35 °C