



Contactor 25A, 3NO, 230V~50Hz

Technical Characteristics

Frequency	50 Hz
Type of lamp	
Max. power fluo. duo lamp comp. series	
Tightening torque	1,2Nm
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 10mm ²
Type of connection	with screw
Type of contacts	3NO
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2X
Protection class	isol.class II