



RCCB 2P 25A 100mA A Class

Technical Characteristics

| | |
|---|----------------------------------|
| Neutral position | right |
| Fixing mode | DIN rail type O (symmetrical) |
| Frequency | 50 Hz |
| Short-time delayed tripping | No |
| Residual current trip mode | Undelayed |
| Colour | |
| Tightening torque | 2,8Nm |
| Connection cross-sect. flexible conductor | 1 / 16mm ² |
| Connection cross-sect. rigid cable | 1 / 25mm ² |
| Type of connection | with screw |
| European directive WEEE | concerned |
| Protection index IP | IP20 |
| Residual current type | A |