

P64AX/1.0LSF/5

P64AX c/w 4 Core 1.00mm² 5m LSOH Lead



Main electrical features

Rated operational voltage U_e 207 / 230 / 253 V

Rated current 6 A

Materials

Colour pure white

Connection

Cable End Prepared - end of barrel closed

Cable

Conductor Size 1 mm²

Cable Material Low Smoke Zero Halogen

Equipment

Number of terminations -plugs 4

Contact Material Phosphor Bronze

Use

Mechanical Load	5 Kg maximum
<hr/>	
Safety	
Inflammability	UL 94 V0
<hr/>	
Identification	
Application, usage	Light control
<hr/>	