

# P64AX/3.0

**P64AX c/w 4 Core 0.75mm<sup>2</sup> 3m PVC Lead**



## Main electrical features

Rated operational voltage U<sub>e</sub> 207 / 230 / 253 V

Rated current 6 A

## Materials

Colour pure white

## Connection

Cable End Prepared - end of barrel closed

## Cable

Conductor Size 0.75 mm<sup>2</sup>

Cable Material PVC

Cable length 3000 mm

## Equipment

Number of terminations -plugs 4

Contact Material Phosphor Bronze

---

Use

**Mechanical Load**                      5 Kg maximum

---

Safety

**Inflammability**                      UL 94 V0

---

Identification

**Application, usage**                      Light control

---